

YCA391A2N, Compression terminal for AL, ACSR, 6201, 5005, 2-Hole, 1/2" Stud, 1-3/4" Spacing

By Burndy
Catalog # [YCA391A2N](#)

Compression Terminals for Aluminum, ACSR, 6201, 5005, Compressed and Compact Conductors, 795 (37) 750 (61) AL, 10-1/8 in L

Features

- Compression Terminal, 2-Hole NEMA Pad, 1/2" Stud, 1-3/4" Spacing

Application

For AAC(STR,Compressed,compact), ACSR AND AAAC

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - AL Str Size	• 750 kcmil • 795 kcmil
Conductor - AL Str Size Range	• 750 kcmil • 795 kcmil

Configuration

Physical Attribute - Pad Configuration	2 Hole NEMA
Connector Type	Terminal

Dimensions

Package Length	0.000 in
----------------	----------



Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall mm	256 mm
Dimension - Pad Width inch	2.32 in
Package Height	0.000 in
Dimension - B Length inch	5.24 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Length Overall inch	10.06 in

General

Die Index	342
Trade Name	HYLUG™
Prefilled Oxide Inhibitor	Y
Sub Brand	COMPRESSION TERMINAL
Plated	N
Type	YCA-R-N
UPC 12 Digit	781810810392
UPC 14 Digit GTIN	00781810810392
Material	Aluminum
Plating Type	Unplated
UPC	781810810392

Logistics

Minimum Pack Quantity	1
Carton Quantity	40
Pallet Quantity	900

Product Assets

[Catalog \[English\]](#)