



YCA43R2N, Al compression lug, 2-Hole, 1/2" Stud, 1-3/4" Spacing

By Burndy
Catalog # [YCA43R2N](#)

AL compression lug designed for terminating jumper loop and equipment taps to switch pads and other substation switch yard apparatus, 10.28 IN L



Features

- Aluminum Compression Lug
- 2-Hole, 1/2" Stud, 1-3/4" Spacing

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Str Size	605 (30-19) kcmil 636 (24-7) kcmil 636 (26-7) kcmil 636 (30-19) kcmil 666.6 (24-7) kcmil
Conductor - ACSR Str Size Range	605 (30-19) kcmil 636 (24-7) kcmil 636 (26-7) kcmil 636 (30-19) kcmil 666.6 (24-7) kcmil
Conductor - AL Str Size	700 kcmil 750 kcmil 795 kcmil
Conductor - AL Str Size Range	700 kcmil 750 kcmil 795 kcmil

Configuration

Physical Attribute - Pad Configuration	2 Hole NEMA
--	-------------

Connector Type

Terminal

Dimensions

Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall mm	260 mm
Dimension - Pad Width inch	2.48 in
Package Height	0.000 in
Dimension - B Length inch	5.30 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Length Overall inch	10.28 in

General

Die Index	292 319
Trade Name	HYLUG™
Prefilled Oxide Inhibitor	Y
Plated	N
UPC 12 Digit	781810016671
UPC 14 Digit GTIN	00781810016671
Material	Aluminum
Plating Type	Unplated
UPC	781810016671

Logistics

Minimum Pack Quantity	1
Carton Quantity	6
Pallet Quantity	1008

Product Assets

[Catalog \[English\]](#)