



YCA451A4N, Al compression terminal, 4-Hole, 1/2" Stud, 1-3/4" Spacing, 113 ACSR, 1272 kcmil AL

By Burndy
Catalog # [YCA451A4N](#)

Aluminum Terminal, 4 Pad Holes, 1113 (54-19) kcmil ACSR, 1272 (61) kcmil AL., 422 Index

Features

- Aluminum Compression Terminal
- 4-Hole, 1/2" Stud, 1-3/4" Spacing

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Str Size	1113 (54-19) kcmil
Conductor - ACSR Str Size Range	1113 (54/19) kcmil
Conductor - AL Str Size	1272 (61) kcmil

Configuration

Physical Attribute - Pad Configuration	4 Hole NEMA
Connector Type	Terminal

Dimensions

Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in

Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - B Length inch	4.92 in
Dimension - L Length Overall mm	259 mm
Dimension - Pad Width inch	3 in
Package Height	0.000 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Length Overall inch	10.19 in

General

Die Index	422
Trade Name	HYLUG™
Plated	N
Prefilled Oxide Inhibitor	Y
UPC 12 Digit	781810016725
UPC 14 Digit GTIN	00781810016725
Material	Aluminum
Plating Type	Unplated
UPC	781810016725

Logistics

Minimum Pack Quantity	1
Carton Quantity	8
Pallet Quantity	720

Product Assets

[Catalog \[English\]](#)



A Hubbell brand