

YCA45R2N, Al compression Lug, 2-Hole, 1/2" Stud, 1-3/4" Spacing

By Burndy

Catalog # [YCA45R2N](#)

AL compression lug designed for terminating jumper loop and equipment taps to switch pads and other substation switch yard apparatus, Index: 352



Features

- Aluminum compression HYLUG
- NEMA Standard Mounting Holes

Application

For AAC(STR,Compressed,compact), ACSR AND AAAC

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Str Size	795 (54-7) kcmil 795 (26-/7) kcmil
Conductor - ACSR Str Size Range	795 (54-7) kcmil 795 (26-/7) kcmil
Conductor - AL Str Size	900 kcmil 954 kcmil 1000 kcmil
Conductor - AL Str Size Range	900 kcmil 954 kcmil 1000 kcmil

Configuration

Physical Attribute - Pad Configuration	2 Hole NEMA
Connector Type	Terminal

Dimensions

Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall mm	261 mm
Dimension - Pad Width inch	2.55 in
Package Height	0.000 in
Dimension - B Length inch	5.31 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Length Overall inch	10.28 in

General

Die Index	352
Trade Name	HYLUG™
Prefilled Oxide Inhibitor	Y
Sub Brand	TERMINALS
Plated	N
Type	YCA-R-N
UPC 12 Digit	781810016701
UPC 14 Digit GTIN	00781810016701
Material	Aluminum
Plating Type	Unplated
UPC	781810016701

Logistics

Minimum Pack Quantity	1
Carton Quantity	10
Pallet Quantity	900

Product Assets

[Catalog \[English\]](#)