



YCAB314N, Cast Copper Tongue Terminal with Copper Sleeve, 4-Hole, 1/2" Stud, 1-3/4" Spacing, 350 kcmil

By Burndy
Catalog # [YCAB314N](#)

Cast Cu Alloy Tongue Terminal With Cu Sleeve, 4 NEMA Holes, 350 Kcmil Cu(12, 19, 37 Str), 1/2" Stud, 1.75" Spacing, 267 Index

Features

- Cast Copper Alloy Tongue Terminal with Copper Sleeve
- 4-Hole, 1/2" Stud, 1-3/4" Spacing

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	350 kcmil
Conductor - Copper Str Size	350 kcmil

Configuration

Physical Attribute - Number of Holes	4
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3.00 in
Package Height	0.000 in
Dimension - Hole Size fraction	14/25 in
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	2-33/50 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in

Package Width	0.000 in
Dimension - Z inch	0.63 in
Dimension - L Length Overall mm	178 mm
Dimension - B Length inch	2.66 in
Dimension - Outside Diameter inch	1.17 in
Dimension - D inch	2.00 in
Dimension - N inch	0.62 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	7.00 in
Dimension - Strip Length inch	1 3/16
Dimension - Stud Size inch	1/2

General

Plated	N
Trade Name	HYLUG™
Die Index	267
UPC	781810035382
Prefilled Oxide Inhibitor	N
Material	Copper Alloy
Plating Type	Unplated
UPC 14 Digit GTIN	00781810035382

Logistics

Minimum Pack Quantity	1
Pallet Quantity	612
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)