




YCAB344N, Cu Compression Lug, 4-Hole, 1/2" Stud, 1-3/4" Spacing

By Burndy
Catalog # [YCAB344N](#)

Copper compression lug designed for terminating copper conductors to switch pads and other substation switch yard apparatus, Pad width: 3 IN.



Features

- NEMA Standard mounting holes
- Made of pure copper

Application

For Terminating Copper Conductors To Switch Pads And Other Substation Or Switch Yard Apparatus

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	500 kcmil
Conductor - Copper Str Size Range	500 kcmil

Configuration

Physical Attribute - Number of Holes	4
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3.00 in
Package Height	0.000 in
Dimension - Hole Size fraction	14/25 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in

Package Width	0.000 in
Dimension - L Length Overall mm	173 mm
Dimension - Outside Diameter inch	1.38 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Strip Length inch	2 5/8
Dimension - Stud Size inch	1/2
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	2-9/17 in
Dimension - Z inch	0.63 in
Dimension - B Length inch	2.53 in
Dimension - D inch	3.00 in
Dimension - N inch	0.62 in
Dimension - Length Overall inch	6.81 in

General

Trade Name	HYLUG™
Die Index	210
Prefilled Oxide Inhibitor	N
Plated	No
Physical Attribute - Tongue Type	Standard
Sub Brand	HYLUG
Product Type	Compression
UPC	781810014851
Type	YCAB-4N
Material	Copper
Plating Type	Tin
UPC 14 Digit GTIN	00781810014851

Logistics

Minimum Pack Quantity	1
Pallet Quantity	576
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)