



YCAK25R4N, Al compression lug, 4-Hole,
1/2" Stud, 1-3/4" Spacing

By Burndy
Catalog # [YCAK25R4N](#)

Aluminum compression lug designed for terminating jumper loop and equipment taps to switch pads and other substation switch yard apparatus.

Features

- Aluminum Compression Lug
- 4-Hole, 1/2" Stud, 1-3/4" Spacing

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Str Size	1/0 (6/1) AWG
Conductor - ACSR Str Size Range	1/0 (6/1) AWG
Conductor - AL Str Size	1/0 AWG
Conductor - AL Str Size Range	1/0 AWG

Configuration

Physical Attribute - Pad Configuration	4 Hole NEMA
--	-------------

Dimensions

Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in

Package Weight	0.000 lb.
Dimension - B Length inch	2.62 in
Dimension - L Length Overall mm	174 mm
Dimension - Pad Width inch	3 in
Package Height	0.000 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Length Overall inch	6.86 in

General

Die Index	• 243 • BG
Trade Name	HYLUG™
Plated	N
Prefilled Oxide Inhibitor	Y
UPC 12 Digit	781810081433
UPC 14 Digit GTIN	00781810081433
Material	Aluminum
Plating Type	Unplated
UPC	781810081433

Logistics

Minimum Pack Quantity	1
Carton Quantity	25
Pallet Quantity	900

Product Assets

[Catalog \[English\]](#)