



YCAK26R4N, Al terminal, 4-Hole, 1/2" Stud, 1-3/4" Spacing, 2/0 AWG ACSR, AL

By Burndy
Catalog # [YCAK26R4N](#)

Aluminum Terminal, 4 Pad Holes, 2/0 (6-1) AWG ACSR, 2/0 (7,19) AWG AL., 245 Index

Features

- Aluminum Compression Terminal
- 4-Hole, 1/2" Stud, 1-3/4" Spacing

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Str Size	2/0 AWG
Conductor - AL Str Size	2/0 AWG

Dimensions

Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - B Length inch	2.60 in

Dimension - L Length Overall mm	174 mm
Dimension - Pad Width inch	3 in
Package Height	0.000 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Length Overall inch	6.86 in

General

Die Index	245
Trade Name	HYLUG™
Plated	N
Prefilled Oxide Inhibitor	Y
UPC 12 Digit	781810016930
UPC 14 Digit GTIN	00781810016930
Material	Aluminum
Plating Type	Unplated
UPC	781810016930

Logistics

Minimum Pack Quantity	3
Carton Quantity	10
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)