



YCAK27R2G2, Al compression terminal, 2-Hole, 3/0 AWG Cu/Al, 3/0 AWG

By Burndy
Catalog # [YCAK27R2G2](#)

Cast Aluminum Compression Terminal, 2 Pad Holes, 3/0 AWG (7,19) Cu & Al, 3/0 (6-1) AWG , 317 or 705 Index

Features

- Aluminum Compression Terminal
- 2-Hole

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Str Size	3/0 AWG
Conductor - AL Str Size	3/0 AWG

Dimensions

Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - B Length inch	3 in

Dimension - L Length Overall mm	184 mm
Package Height	0.000 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Length Overall inch	7.25 in

General

Die Index	• 317 • 705
Trade Name	HYLUG™
Plated	N
Prefilled Oxide Inhibitor	Y
UPC 12 Digit	781810016855
UPC 14 Digit GTIN	00781810016855
Material	Aluminum, Cast
Plating Type	Unplated
UPC	781810016855

Logistics

Minimum Pack Quantity	3
Carton Quantity	1
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)