



YCAK28A2G1, Aluminum terminal, 4/0 Str Cu/Al

By Burndy
Catalog # [YCAK28A2G1](#)

Aluminum Terminal, 4/0 Str. Cu,Al Conc.& Compact, 317 or 705 Index

Features

- Aluminum Compression Terminal

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Str Size	4/0 AWG
Conductor - AL Str Size	4/0 AWG
Conductor - AL Str Size Range	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG

Dimensions

Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall	143 mm

Dimension - Pad Width inch	1.25 in
Package Height	0.000 in
Dimension - B Length fraction	5-5/8 in
Dimension - B Length inch	1.56 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Length Overall inch	5.63 in
Dimension - D inch	3 in

General

Die Index	317 705
Trade Name	HYLUG™
Prefilled Oxide Inhibitor	Y
Plated	N
UPC 12 Digit	781810810248
UPC 14 Digit GTIN	00781810810248
Material	Aluminum
Plating Type	Unplated
UPC	781810810248

Logistics

Minimum Pack Quantity	5
Carton Quantity	20
Pallet Quantity	5040

Product Assets

[Catalog \[English\]](#)