



YCAK28AG1, Al compression terminal, 1-hole, 1/2" Stud, 4/0 AWG ACSR, 4/0 Str Al/Cu

By Burndy
Catalog # [YCAK28AG1](#)

Al Compression Terminal, 1 Hole, 4/0 AWG ACSR, 4/0 Str Al/Cu, 0.56" Hole Dia.

Features

- Aluminum Compression Terminal
- 1-Hole, 1/2" Stud

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Str Size	4/0 AWG (6-1)
Conductor - ACSR Str Size Range	4/0 AWG (6-1)
Conductor - AL Str Size	3/0 (Str) - 4/0 (Str)
Conductor - AL Str Size Range	3/0 AWG - 4/0 AWG

Configuration

Physical Attribute - Pad Configuration	2 Hole NEMA
--	-------------

Dimensions

Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - B Length inch	2 in

Dimension - L Length Overall mm	97 mm
Dimension - Pad Width inch	0.91 in
Physical Attribute - Tongue Angle	Straight
Package Height	0.000 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Length Overall inch	3.83 in

General

Die Index	249 840
Physical Attribute - Tongue Type	Standard
Trade Name	HYLUG™
Plated	N
Prefilled Oxide Inhibitor	Y
UPC 12 Digit	781810226315
UPC 14 Digit GTIN	00781810226315
Material	Aluminum
Plating Type	Unplated
UPC	781810226315

Logistics

Minimum Pack Quantity	25
Carton Quantity	1
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)