



YCAK29A2G1, Al compression lug, prefilled with PENETROX Oxide Inhibitor

By Burndy
Catalog # [YCAK29A2G1](#)

AL compression lug for joining AL and CU cable to transformer and equipment pads, Prefilled with PENETROX, 5.63 IN L

Features

- Aluminum Compression Lug
- Prefilled with PENETROX Oxide Inhibitor

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Str Size	250 kcmil
Conductor - ACSR Str Size	4/0 AWG - 250 kcmil
Conductor - ACSR Str Size Range	4/0 AWG - 250 kcmil
Conductor - AL Str Size	250 kcmil
Conductor - AL Str Size Range	250 kcmil
Conductor - Copper Str Size Range	250 kcmil

Configuration

Physical Attribute - Pad Configuration	2 Hole NEMA
--	-------------

Dimensions

Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Package Weight	0.000 lb.

Dimension - L Length Overall mm	143 mm
Dimension - Pad Width inch	1.25 in
Package Height	0.000 in
Dimension - B Length fraction	5-5/8 in
Dimension - B Length inch	1.56 in
Physical Attribute - Tongue Angle	Straight
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Length Overall inch	5.63 in
Dimension - D inch	3 in

General

Die Index	• 317 • 705
Trade Name	HYLUG™
Prefilled Oxide Inhibitor	Y
Physical Attribute - Tongue Type	Standard
Plated	N
UPC 12 Digit	781810810262
UPC 14 Digit GTIN	00781810810262
Material	Aluminum Alloy, Cast
Plating Type	Unplated
UPC	781810810262

Logistics

Minimum Pack Quantity	1
Carton Quantity	20
Pallet Quantity	720

Product Assets

[Catalog \[English\]](#)