



By Burndy
Catalog # [YCAK30R4N](#)

Aluminum Terminal, 4 Pad Holes, 266.8 (18-1, 6-7, 26-7) kcmil
ACSR, 266.8 (7, 19) kcmil Al., 251 Index

Features

- Aluminum Compression Terminal
- 4-Hole, 1/2" Stud, 1-3/4" Spacing

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Str Size	266.8 (18-1) kcmil 266.8 (6-7) kcmil 266.8 (26-7) kcmil
Conductor - ACSR Str Size Range	266.8 (18-1) kcmil 266.8 (6-7) kcmil 266.8 (26-7) kcmil
Conductor - AL Str Size	266.8 kcmil
Conductor - AL Str Size Range	266 kcmil

Configuration

Physical Attribute - Pad Configuration	4 Hole NEMA
--	-------------

Dimensions

Package Length	0.000 in
----------------	----------

Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - B Length inch	2.65 in
Dimension - L Length Overall mm	187 mm
Dimension - Pad Width inch	3 in
Package Height	0.000 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Length Overall inch	7.38 in

General

Die Index	251
Trade Name	HYLUG™
Plated	N
Prefilled Oxide Inhibitor	Y
UPC 12 Digit	781810016732
UPC 14 Digit GTIN	00781810016732
Material	Aluminum
Plating Type	Unplated
UPC	781810016732

Logistics

Minimum Pack Quantity	1
Carton Quantity	20
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)