



YCAK32R2G1, Aluminum compression terminal, 2-Hole, 3/0 AWG Cu/Al, 350, 397.5, 336.4

By Burndy
Catalog # [YCAK32R2G1](#)

Cast Aluminum Compression Terminal, 2 Pad Holes, 3/0 AWG (7,19) Cu & Al, 350 (19,37) & 397.5 (19) kcmil, 336.4 (18 - 1, 26 - 7), 317 or 705 Index

Features

- Aluminum Compression Terminal
- 2-Hole

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Str Size	336.4 kcmil
Conductor - AL Str Size	350 kcmil 397.5 kcmil
Conductor - AL Str Size Range	350 kcmil - 397.5 kcmil

Dimensions

Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - B Length inch	3 in

Dimension - L Length Overall mm	184 mm
Package Height	0.000 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Length Overall inch	7.25 in

General

Die Index	317 705
Trade Name	HYLUG™
Plated	N
Prefilled Oxide Inhibitor	Y
UPC 12 Digit	781810016619
UPC 14 Digit GTIN	00781810016619
Material	Aluminum, Cast
Plating Type	Unplated
UPC	781810016619

Logistics

Minimum Pack Quantity	1
Carton Quantity	1
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)