



YCAK33R4N, Al compression terminal, 4-Hole, 1/2" Stud, 1-3/4" Spacing, 336.4 kcmil ACSR, 397.5 kcmil Al

By Burndy
Catalog # [YCAK33R4N](#)

Al Compression terminal, 336.4 Kcmil ACSR(26-7, 30-7) str 397.5 Kcmil Al(19)Str, .56"stud, 7.34"L, , 316 index

Features

- Compression Terminal, 4-Hole NEMA Pad, 1/2" Stud, 1-3/4" Spacing

Application

For ACSR/6201/5005 (Compressed/Compact), Aluminum

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Str Size	• 336.4 (26-7) kcmil • 336.4 (30-7) kcmil
Conductor - ACSR Str Size Range	• 336.4 (26-7) kcmil • 336.4 (30-7) kcmil
Conductor - AL Str Size	397.5 kcmil
Conductor - AL Str Size Range	397.5 kcmil

Configuration

Physical Attribute - Pad Configuration	4 Hole NEMA
--	-------------

Dimensions



Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall	187 mm
Dimension - Pad Width inch	3 in
Package Height	0.000 in
Dimension - B Length inch	3.05 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Length Overall	7.34 in

General

Die Index	316
Trade Name	HYLUG™
Prefilled Oxide Inhibitor	Y
Sub Brand	TERMINALS
Plated	N
Type	YCAK-R-N, Terminal
UPC 12 Digit	781810810231
UPC 14 Digit GTIN	00781810810231
Material	Aluminum
Plating Type	Unplated
UPC	781810810231

Logistics

Minimum Pack Quantity	10
Carton Quantity	10
Pallet Quantity	1500

Product Assets

[Catalog \[English\]](#)