



YCAK34A2G3, Al compression terminal,
500 kcmil

By Burndy
Catalog # [YCAK34A2G3](#)

Al Compression terminal, 500 kcmil 500 kcmil COMP, .56"stud,
6.55"L

Features

- Aluminum Compression Terminal

Application

For Copper, Aluminum Concentric And Compact

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Certification - UL Recognized	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Str Size	500 kcmil
Conductor - AL Str Size	500 kcmil
Conductor - AL Str Size Range	500 kcmil
Conductor - Copper Str Size Range	500 kcmil

Configuration

Physical Attribute - Pad Configuration	2 Hole NEMA
--	-------------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.

Dimension - L Length Overall mm	165 mm
Dimension - Pad Width inch	1.50 in
Package Height	0.000 in
Dimension - Hole Size inch	0.56 in
Dimension - B Length fraction	6-1/2 in
Dimension - B Length inch	2.19 in
Physical Attribute - Tongue Angle	Straight
Dimension - Length Overall inch	6.55 in

General

Die Index	608 786
Prefilled Oxide Inhibitor	Y
Sub Brand	TERMINALS
Physical Attribute - Tongue Type	Standard
Plated	N
Type	YCAK-A, Terminal
UPC 12 Digit	781810810309
UPC 14 Digit GTIN	00781810810309
Material	Aluminum
Plating Type	Unplated
UPC	781810810309

Logistics

Minimum Pack Quantity	1
Carton Quantity	1
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)