



YCAK36A2G1, Al compression lug, Prefilled with PENETROX Oxide Inhibitor filled

By Burndy
Catalog # [YCAK36A2G1](#)

AL compression lug for joining AL and CU cable to transformer and equipment pads, Prefilled with PENETROX, 6.55 IN L

Features

- Aluminum Compression Lug
- 2-Hole
- Prefilled with PENETROX Oxide Inhibitor

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - AL Str Size	600 kcmil
Conductor - AL Str Size Range	600 kcmil

Configuration

Physical Attribute - Pad Configuration	2 Hole NEMA
--	-------------

Dimensions

Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Dimension - B Length fraction	6-1/2 in
Package Weight	0.000 lb.
Dimension - B Length inch	2.19 in

Dimension - L Length Overall mm	165 mm
Dimension - Pad Width inch	1.50 in
Physical Attribute - Tongue Angle	Straight
Package Height	0.000 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	6.55 in
Dimension - D inch	3 in

General

Die Index	• 608 • 786
Physical Attribute - Tongue Type	Standard
Trade Name	HYLUG™
Plated	N
Prefilled Oxide Inhibitor	Y
UPC 12 Digit	781810810323
UPC 14 Digit GTIN	00781810810323
Material	Aluminum
Plating Type	Unplated
UPC	781810810323

Logistics

Minimum Pack Quantity	4
Carton Quantity	1
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)