



YCAK37R4N, Al compression lug, 4-Hole,
1/2" Stud, 1-3/4" Spacing

By Burndy
Catalog # [YCAK37R4N](#)

AL compression lug designed for terminating jumper loop and equipment taps to switch pads and other substation switch yard apparatus, 8.09 IN L

Features

- Aluminum compression HYLUG
- NEMA Standard Mounting Holes

Application

Used for terminating jumper loops and equipment taps at switchpads and other substation apparatus, or to YDW-R deadends.

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Str Size	477 kcmil (24-7,26-7,30-7
Range	STR),556.5 kcmil (18-1 STR)
Conductor - AL Str Size	556.5 kcmil (19 STR)

Configuration

Physical Attribute - Pad	4 Hole NEMA
Configuration	

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall	206 mm
mm	
Dimension - Pad Width inch	3 in
Package Height	0.000 in
Dimension - Hole Size inch	0.56 in
Dimension - B Length inch	3.73 in
Dimension - Bolt Hole Size inch	0.5 in
Dimension - Length Overall	8.09 in
inch	

General

Die Index	261
Prefilled Oxide Inhibitor	Y
Sub Brand	COMPRESSION TERMINAL
Plated	N
Type	YCAK-R-N
UPC 12 Digit	781810016763
UPC 14 Digit GTIN	00781810016763
Material	Aluminum
Plating Type	Unplated
UPC	781810016763

Logistics

Minimum Pack Quantity	1
Carton Quantity	12
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)



A Hubbell brand