



YCAK39A2G2, Al Compression Lug for joining cable to transformer and equipment pads

By Burndy
Catalog # [YCAK39A2G2](#)

AL compression lug for joining AL and CU cable to transformer and equipment pads, Prefilled with PENETROX™, 6.96 IN L

Features

- Aluminum Compression Terminal

Application

For Aluminum Concentric And Compact

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - AL Str Size	750 kcmil
Conductor - AL Str Size Range	750 kcmil

Configuration

Physical Attribute - Pad Configuration	2 Hole NEMA
--	-------------

Dimensions

Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Package Weight	0.000 lb.

Dimension - L Length Overall mm	176 mm
Dimension - Pad Width inch	1.50 in
Package Height	0.000 in
Dimension - Hole Size inch	0.56 in
Dimension - B Length fraction	6-15/16 in
Dimension - B Length inch	2.50 in
Physical Attribute - Tongue Angle	Straight
Dimension - Length Overall inch	6.96 in

General

Die Index	608 786
Trade Name	HYLUG™
Prefilled Oxide Inhibitor	Y
Sub Brand	TERMINALS, HYLUG
Physical Attribute - Tongue Type	Standard
Plated	N
Type	YCAK-A, Terminal
UPC 12 Digit	781810810347
UPC 14 Digit GTIN	00781810810347
Material	Aluminum
Plating Type	Unplated
UPC	781810810347

Logistics

Minimum Pack Quantity	1
Carton Quantity	20
Pallet Quantity	2500

Product Assets

[Catalog \[English\]](#)