



YCAK43R4N, Aluminum terminal, 4-Hole,  
1/2" Stud, 1-3/4" Spacing

By Burndy  
Catalog # [YCAK43R4N](#)

Aluminum Terminal, 4 Pad Holes, 605 (30-19), 636 (24-7, 26-7, 30-19), 666.6 (24-7) kcmil ACSR, 795 (37, 61), 700 (61), 750 (61) kcmil Al., 292 or 319 Index

Features

- Aluminum Compression Terminal
- 4-Hole, 1/2" Stud, 1-3/4" Spacing

Specifications

|                                    |    |
|------------------------------------|----|
| Certification - cULus              | No |
| Certification - UL Recognized      | No |
| Certification - ETL                | No |
| Standards - RoHS Compliance Status | CM |
| Certification - CSA Approved       | No |
| UL Listed                          | No |

Conductor

|                                 |                                                                              |
|---------------------------------|------------------------------------------------------------------------------|
| Conductor - ACSR Str Size Range | 605 kcmil (30-19 STR),636 kcmil (24-7,26-7,30-19 STR),666.6 kcmil (24-7 STR) |
| Conductor - AL Str Size Range   | 795 kcmil (37,61 STR),700 kcmil (61 STR),750 kcmil (61 STR)                  |

Configuration

|                                        |             |
|----------------------------------------|-------------|
| Physical Attribute - Pad Configuration | 4 Hole NEMA |
|----------------------------------------|-------------|

Dimensions

|                |          |
|----------------|----------|
| Package Length | 0.000 in |
| Package Width  | 0.000 in |

|                                 |           |
|---------------------------------|-----------|
| Package Weight                  | 0.000 lb. |
| Dimension - L Length Overall mm | 244 mm    |
| Dimension - Pad Width inch      | 3 in      |
| Package Height                  | 0.000 in  |
| Dimension - Bolt Hole Size inch | 0.5 in    |
| Dimension - Hole Size inch      | 0.56 in   |
| Dimension - Length Overall inch | 9.625 in  |

General

|                           |                                                                 |
|---------------------------|-----------------------------------------------------------------|
| Die Index                 | <ul style="list-style-type: none"><li>292</li><li>319</li></ul> |
| Plated                    | N                                                               |
| Prefilled Oxide Inhibitor | Y                                                               |
| UPC 12 Digit              | 781810016787                                                    |
| UPC 14 Digit GTIN         | 00781810016787                                                  |
| Material                  | Aluminum                                                        |
| Plating Type              | Unplated                                                        |
| UPC                       | 781810016787                                                    |

Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 2   |
| Carton Quantity       | 8   |
| Pallet Quantity       | 896 |

Product Assets

[Catalog \[English\]](#)