



YCAK45R4N, Al Compression Terminal, 4-Hole, 1/2" Stud, 1-3/4" Spacing

By Burndy
Catalog # [YCAK45R4N](#)

Aluminum Compression Terminal, 795 (26-7, 54-7) ACSR 900(61, 91), 954(37, 61), 1000(61) Al, 1/2" Stud

Features

- Aluminum Compression Lug, NEMA Standard 4-Hole Pad, 1/2" Stud, 1-3/4" Spacing

Application

For AAC(STR,Compressed,compact), ACSR AND AAAC

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Str Size	795 kcmil (54-7 STR)
Conductor - AL Str Size Range	900 kcmil (61,91 STR), 954 kcmil (37,61 STR),1000 kcmil (61 STR)

Configuration

Physical Attribute - Pad Configuration	4 Hole NEMA
--	-------------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall	254 mm
Dimension - Pad Width inch	4.00 in
Package Height	0.000 in
Dimension - Hole Size inch	0.56 in
Dimension - B Length inch	5.25 in
Dimension - Bolt Hole Size inch	0.5 in
Dimension - Length Overall	9.64 in

General

Die Index	352
Prefilled Oxide Inhibitor	Y
Sub Brand	COMPRESSION TERMINAL
Plated	N
Type	YCAK-R-N
UPC 12 Digit	781810016794
UPC 14 Digit GTIN	00781810016794
Material	Aluminum
Plating Type	Unplated
UPC	781810016794

Logistics

Minimum Pack Quantity	1
Carton Quantity	8
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)