



YCB1U1, Aluminum CRIMPIT™ Series Hot Tap,ACSR: 2 (6-1) AWG-2 (7-1) AWG, AL or CU: 2 AWG-1 AWG

By Burndy
Catalog # [YCB1U1](#)



Aluminum CRIMPIT™ Hot Tap, ACSR: 2 (6-1) AWG-2 (7-1) AWG, AL or CU: 2 AWG-1 AWG

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 2 AWG • 1 AWG
Conductor - AL Str Size Range	2 AWG-1 AWG
Conductor - ACSR Str Size	• 2 (6/1) Sparrow AWG • 2 (7/1) Sparate AWG
Conductor - ACSR Str Size Range	2 (6/1) Sparrow AWG-2 (7/1) Sparate AWG

Dimensions

Dimension - Height mm	41.3 mm
Dimension - Height inch	1.625 in
Dimension - F Width Center to Center inch	4.00 in
Dimension - Bail Size	2

Dimension - L Length Overall mm	46 mm
Dimension - Length Overall inch	1.81 in

General

Plated	N
Trade Name	CRIMPIT™
Series	CRIMPIT™ Series
Die Index	D
UPC	781810151471
Type	Stirrups
Prefilled Oxide Inhibitor	N
Material	Aluminum
Material - Bail	Copper
Plating Type	Unplated
UPC 12 Digit	781810151471
UPC 14 Digit GTIN	00781810151471

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3600
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)