



YCB25R, Al Stirrup Connector, 1/0 AWG Al, 1/0 ACSR

By Burndy
Catalog # [YCB25R](#)



Stirrup Connector,Aluminum:1/0 AWG, ACSR:1/0 (6-1) AWG-80 (8-1) kcmil ACSR

Features

- Permanent compression hot-line clamp adapter with aluminum run and copper bail
- Accommodates any standard copper hotline clamp on bail elements
- Permits hotline tapping without arcing or chafing damage to aluminum conductor
- Installed with standard tools and dies

Application

For Aluminum, ACSR, 6201, 5005, Compressed And Compact Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	1/0 AWG
Conductor - AL Str Size Range	1/0 AWG
Conductor - ACSR Str Size	• 1/0 (6/1) Raven AWG • 2/0 (6/1) Quail AWG • 3/0 (6/1) Pigeon AWG • 4/0 (6/1) Penguin AWG • 80 (8/1) Grouse kcmil
Conductor - ACSR Str Size Range	1/0 (6/1) Raven AWG-80 (8/1) Grouse kcmil

Dimensions

Package Height	0.000 in
Dimension - Height mm	125 mm
Dimension - Height inch	4.91 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	3.50 in
Package Width	0.000 in
Dimension - L Length Overall mm	246 mm
Dimension - Bail Size	2
Dimension - D inch	2.50 in
Dimension - Length Overall inch	9.69 in

General

Die Index	C
Prefilled Oxide Inhibitor	N
Plated	N
Sub Brand	CRIMPIT
UPC	781810151716
Type	Stirrups
Material	Aluminum
Material - Bail	Copper
Plating Type	Unplated
UPC 12 Digit	781810151716
UPC 14 Digit GTIN	00781810151716

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1680
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)