



YCB27AU2G1,Cable CRIMPIT™ Series,
1/0(6-1) AWG,-2/0(6-1) AWG ACSR, 1/0(19)
AWG-3/0(19) AWG Cu or Al

By Burndy
Catalog # [YCB27AU2G1](#)



Cable CRIMPIT™, 1/0(6-1) AWG,-2/0(6-1) AWG ACSR, 1/0(19)
AWG-3/0(19) AWG Cu or Al

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size Range	1/0 AWG - 3/0 AWG
Conductor Type	• ACSR Str-Size • AL Str-Size • CU Str-Size
Conductor - ACSR Str Size	• 1/0 (6-1) AWG • 2/0 (6-1) AWG
Conductor - Copper Str Size Range	1/0 AWG-3/0 AWG
Conductor - ACSR Str Size Range	1/0 (6-1) AWG-2/0 (6-1) AWG

Dimensions

Dimension - Height mm	0 mm
Dimension - Height inch	1.70 in
Dimension - Width mm	25 mm
Dimension - Width inch	0.97 in
Dimension - F Width Center to Center inch	4.00 in

Dimension - Bail Size	0.258 in
Dimension - L Length Overall mm	68 mm
Dimension - D inch	4.25 in
Dimension - Length Overall inch	2.69 in

General

Plated	N
Trade Name	CRIMPIT™
Series	CRIMPIT™ Series
Die Index	D3
UPC	781810014066
Type	Stirrups
Prefilled Oxide Inhibitor	N
Material	Aluminum
Material - Bail	Copper
Plating Type	Unplated
UPC 12 Digit	781810014066
UPC 14 Digit GTIN	00781810014066

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3600
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)