



YCB28R, Aluminum Stirrup Connector, 4/0 AWG, 4/0 ACSR

By Burndy
Catalog # [YCB28R](#)



Stirrup Connector,Aluminum:4/0 AWG, ACSR:4/0 AWG

Features

- Permanent compression hot-line clamp adapter with aluminum run and copper bail
- Accommodates any standard copper hotline clamp on bail elements
- Permits hotline tapping without arcing or chafing damage to aluminum conductor
- Installed with standard tools and dies

Application

For Aluminum, ACSR, 6201, 5005, Compressed And Compact Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	4/0 AWG
Conductor - AL Str Size Range	4/0 AWG
Conductor - ACSR Str Size	4/0 (6/1) Penquin AWG
Conductor - ACSR Str Size Range	4/0 (6/1) Penquin AWG
Conductor Size	4/0 AWG

Dimensions

Package Height	0.000 in
----------------	----------

Dimension - Height mm	0 mm
Dimension - Height inch	5 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	3.50 in
Package Width	0.000 in
Dimension - L Length Overall mm	283 mm
Dimension - Width mm	29 mm
Dimension - Width inch	1.14 in
Dimension - Bail Size	0.324 in
Dimension - D inch	3.50 in
Dimension - Length Overall inch	11.14 in

General

Die Index	L
Prefilled Oxide Inhibitor	N
Plated	N
Sub Brand	CRIMPIT
UPC	781810152515
Type	Stirrups
Material	Aluminum
Material - Bail	Copper
Plating Type	Unplated
UPC 12 Digit	781810152515
UPC 14 Digit GTIN	00781810152515

Logistics

Minimum Pack Quantity	8
Pallet Quantity	1
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)



A Hubbell brand