



YCB28U26, Cable CRIMPIT™ Series, 1/0(6-1)
AWG-4/0(6-1) AWG, ACSR: 1/0 AWG-4/0
AWG Cu or Al

By Burndy
Catalog # [YCB28U26](#)

Cable CRIMPIT™, 1/0(6-1) AWG-4/0(6-1) AWG, ACSR: 1/0 AWG-
4/0 AWG Cu or Al



Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	1/0 AWG 2/0 AWG 3/0 AWG 4/0 AWG
Conductor - AL Str Size Range	1/0 AWG - 4/0 AWG
Conductor Type	- ACSR Str-Size - AL Str-Size - CU Str-Size
Conductor - ACSR Str Size	1/0 (6/1) Raven AWG 2/0 (6/1) Quail AWG 3/0 (6/1) Pigeon AWG 4/0 (6/1) Penguin AWG
Conductor - Copper Str Size Range	1/0 AWG-4/0 AWG
Conductor - Copper Str Size	1/0 AWG 2/0 AWG 3/0 AWG 4/0 AWG
Conductor - ACSR Str Size Range	1/0 (6/1) Raven AWG-4/0 (6/1) Penguin AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	50.8 mm

Dimension - Height inch	2.06 in
Dimension - Height fraction	2
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	4.00 in
Package Width	0.000 in
Dimension - Bail Size	0.258 in
Dimension - L Length Overall mm	54 mm
Dimension - D inch	4.25 in
Dimension - Length Overall inch	2.125 in

General

Plated	N
Trade Name	CRIMPIT™
Series	CRIMPIT™ Series
Die Index	H
UPC	781810152584
Type	Stirrups
Prefilled Oxide Inhibitor	N
Material	Aluminum
Material - Bail	Copper
Plating Type	Tin
UPC 12 Digit	781810152584
UPC 14 Digit GTIN	00781810152584

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3600
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)