



YCB28U2G1, Cable CRIMPIT™ Series, 3/0(6-1) AWG-4/0(6-1) AWG, ACSR: 4/0 AWG Cu or Al

By Burndy
Catalog # [YCB28U2G1](#)

Cable CRIMPIT™, 3/0(6-1) AWG-4/0(6-1) AWG, ACSR: 4/0 AWG Cu or Al

Features

- Combines Figure 6-Shaped aluminum CRIMPIT Tap Connector with Tin-Plated Copper Bail
- Can be gripped in tool and slipped over line for easy installation
- Prefilled with PENETROX Joint Compound and stripsealed

Application

For Aluminum, ACSR, 6201, 5005, Compressed And Compact Conductors

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	4/0 AWG
Conductor Type	• ACSR Str-Size • AL Str-Size • CU Str-Size
Conductor - ACSR Str Size	• 3/0 (6-1) AWG • 4/0 (6-1) AWG
Conductor - Copper Str Size	4/0 AWG
Conductor - ACSR Str Size Range	3/0 (6-1) AWG-4/0 (6-1) AWG

Dimensions

Dimension - Height mm	0 mm
-----------------------	------



Dimension - Height inch	1.70 in
Dimension - Width mm	25 mm
Dimension - Width inch	0.97 in
Dimension - F Width Center to Center inch	4.00 in
Dimension - Bail Size	0.258 in
Dimension - L Length Overall mm	68 mm
Dimension - D inch	4.25 in
Dimension - Length Overall inch	2.69 in

General

Plated	N
Trade Name	CRIMPIT™
Sub Brand	COMPRESSION TAP CONNECTOR, CABELOK CRIMPIT
Series	CRIMPIT™ Series
Die Index	D3
UPC	781810014073
Type	Stirrups
Prefilled Oxide Inhibitor	N
Material	Aluminum
Material - Bail	Copper
Plating Type	Unplated
UPC 12 Digit	781810014073
UPC 14 Digit GTIN	00781810014073

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3600
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)