



YCB2U3G1, Cable CRIMPIT™ Series, 6(6-1)
AWG,-2(7-1) AWG ACSR, 6(7) AWG-3(7)
AWG Cu or Al

By Burndy
Catalog # [YCB2U3G1](#)



Cable CRIMPIT™, 6(6-1) AWG,-2(7-1) AWG ACSR, 6(7) AWG-3(7)
AWG Cu or Al

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Dimension - F Width Center to Center inch	4.00 in
Package Width	0.000 in
Dimension - Bail Size	0.258 in
Dimension - L Length Overall mm	63.5 mm
Dimension - D inch	4.25 in
Dimension - Length Overall inch	2.50 in

Conductor

Conductor - AL Str Size	• 6 AWG • 3 AWG
Conductor - AL Str Size Range	6 AWG-3 AWG
Conductor Type	• ACSR Str-Size • AL Str-Size • CU Str-Size
Conductor - ACSR Str Size	• 6 (6-1) AWG • 2 (7-1) AWG
Conductor - Copper Str Size	• 6 AWG • 3 AWG
Conductor - ACSR Str Size Range	6 (6-1) AWG-2 (7-1) AWG

General

Plated	N
Trade Name	CRIMPIT™
Series	CRIMPIT™ Series
Die Index	O
UPC	781810014042
Type	Stirrups
Prefilled Oxide Inhibitor	N
Material	Aluminum
Material - Bail	Copper
Plating Type	Unplated
UPC 12 Digit	781810014042
UPC 14 Digit GTIN	00781810014042

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Height inch	1.30 in
Package Weight	0.000 lb.
Dimension - Width mm	18 mm
Dimension - Width inch	0.72 in
Package Length	0.000 in

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3600
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)