



YCB321R, Aluminum Stirrup Connector,
336.4-350 kcmil Aluminum, ACSR:
300(26/7) kcmil, 336 (26/7, 26/7) 336.4
(18/1)



By Burndy
Catalog # [YCB321R](#)

Stirrup Connector,Aluminum:336.4 kcmil-350 kcmil,
ACSR:300(26/7) kcmil, 336.4(18/1) kcmil

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	336.4 kcmil 350 kcmil
Conductor - AL Str Size Range	336.4 kcmil - 350 Kcmil
Conductor - ACSR Str Size	300.0 (26/7) Ostrich kcmil 336.4 (18/1) Merlin kcmil
Conductor - ACSR Str Size Range	300.0 (26/7) Ostrich kcmil- 336.4 (18/1) Merlin kcmil

Dimensions

Package Height	0.000 in
Dimension - Height mm	136.5 mm
Length	12.75 in
Dimension - Height inch	5.39 in
Package Weight	0.000 lb.
Dimension - Width mm	33 mm
Dimension - Width inch	1.31 in
Package Length	0.000 in
Dimension - F Width Center to Center inch	3.50 in

Package Width	0.000 in
Dimension - Bail Size	0.324 in
Dimension - L Length Overall mm	324 mm
Height	5.39 in
Width	1.28 in
Dimension - D inch	3.50 in
Dimension - Length Overall inch	12.75 in
Dimensions	12.75 in x 1.28 in x 5.39 in

General

Plated	N
Die Index	M
UPC	781810153017
Type	Stirrups
Prefilled Oxide Inhibitor	N
Material	Aluminum
Material - Bail	Copper
Plating Type	Unplated
UPC 12 Digit	781810153017
UPC 14 Digit GTIN	00781810153017

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)