



YCB33R, Aluminum Stirrup Connector,
397.5-400 kcmil Aluminum, ACSR: 336
(26/7, 30/7) 397.5 (18/1)

By Burndy
Catalog # [YCB33R](#)

Stirrup Connector,Aluminum:397.5 kcmil-400 kcmil,
ACSR:336.4(26/7) kcmil, 336.4(30/7) kcmil, 397.5(18/1) kcmil



Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	397 kcmil 400 kcmil
Conductor - AL Str Size Range	397 kcmil - 400 kcmil
Conductor - ACSR Str Size	336.4 (26/7) Linnet kcmil 336.4 (30/7) Oriole kcmil 397.5 (18/1) Chickadee kcmil
Conductor - ACSR Str Size Range	336.4 (26/7) Linnet kcmil-397.5 (18/1) Chickadee kcmil

Dimensions

Package Height	0.000 in
Dimension - Height mm	136.5 mm
Length	12.75 in
Dimension - Height inch	5.39 in
Package Weight	0.000 lb.
Dimension - Width mm	33 mm
Dimension - Width inch	1.31 in
Package Length	0.000 in
Dimension - F Width Center to Center inch	3.50 in

Package Width	0.000 in
Dimension - Bail Size	0.324 in
Dimension - L Length Overall mm	324 mm
Height	5.39 in
Width	1.31 in
Dimension - D inch	3.50 in
Dimension - Length Overall inch	12.75 in
Dimensions	12.75 in x 1.31 in x 5.39 in

General

Plated	N
Die Index	M
UPC	781810152768
Type	Stirrups
Prefilled Oxide Inhibitor	N
Material	Aluminum
Material - Bail	Copper
Plating Type	Unplated
UPC 12 Digit	781810152768
UPC 14 Digit GTIN	00781810152768

Logistics

Minimum Pack Quantity	6
Pallet Quantity	910
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)