



YCB4U1,CRIMPIT™ Series HOT TAP, 4 (6-1) AWG, 4(7-1) AWG ACSR,4 AWG Cu or Al

By Burndy  
Catalog # [YCB4U1](#)



CRIMPIT™ HOT TAP, 4 (6-1) AWG, 4(7-1) AWG ACSR,4 AWG Cu or Al

Specifications

|                                    |    |
|------------------------------------|----|
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Standards - RoHS Compliance Status | CM |
| Certification - cULus              | No |
| UL Listed                          | No |
| Certification - CSA Approved       | No |

Conductor

|                                 |                                                                                                             |
|---------------------------------|-------------------------------------------------------------------------------------------------------------|
| Conductor - ACSR Cmpt Size      | 4 AWG                                                                                                       |
| Conductor - AAAC 6201 Size      | 48.69 (7) kcmil                                                                                             |
| Conductor - AL Str Size         | 4 AWG                                                                                                       |
| Conductor - AL Str Size Range   | 4 AWG                                                                                                       |
| Conductor Type                  | <ul style="list-style-type: none"><li>• ACSR Str-Size</li><li>• AL Str-Size</li><li>• CU Str-Size</li></ul> |
| Conductor - ACSR Str Size       | <ul style="list-style-type: none"><li>• 4 (6/1) Swan AWG</li><li>• 4 (7/1) Swanate AWG</li></ul>            |
| Conductor - Copper Str Size     | 4 AWG                                                                                                       |
| Conductor - ACSR Str Size Range | 4 (6/1) Swan AWG-4 (7/1) Swanate AWG                                                                        |

Dimensions

|                                           |         |
|-------------------------------------------|---------|
| Dimension - Height mm                     | 38.1 mm |
| Dimension - Height inch                   | 1.47 in |
| Dimension - F Width Center to Center inch | 4.00 in |

|                                 |          |
|---------------------------------|----------|
| Dimension - Bail Size           | 0.258 in |
| Dimension - L Length Overall mm | 46 mm    |
| Dimension - D inch              | 4.25 in  |
| Dimension - Length Overall inch | 1.81 in  |

General

|                           |                 |
|---------------------------|-----------------|
| Plated                    | N               |
| Trade Name                | CRIMPIT™        |
| Series                    | CRIMPIT™ Series |
| Die Index                 | D               |
| UPC                       | 781810151655    |
| Type                      | Stirrups        |
| Prefilled Oxide Inhibitor | N               |
| Material                  | Aluminum        |
| Material - Bail           | Copper          |
| Plating Type              | Tin             |
| UPC 12 Digit              | 781810151655    |
| UPC 14 Digit GTIN         | 00781810151655  |

Logistics

|                       |      |
|-----------------------|------|
| Minimum Pack Quantity | 2000 |
| Pallet Quantity       | 3600 |
| Carton Quantity       | 25   |

Product Assets

[Catalog \[English\]](#)