



YCHC29TC29, Cu Compression C Tap, 250 kcmil-2 AWG Run and Tap

By Burndy

Catalog # [YCHC29TC29](#)

Copper Compression C Tap, 250 kcmil- 2 AWG (Main), 250 kcmil- 2 AWG (Tap), Tin Plated



Features

- Range taking C-tap that allows for less inventory as one C-tap can accommodate a multitude of wire combinations
- Manufactured from high conductivity wrought copper providing low resistance for excellent electrical conductivity
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping

Application

Wire Tap

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	BABA Compliant (All status valid till December 2026)
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Flex K Tap Range	2 AWG-4/0 AWG
Conductor - Copper Flex M Run Range	2 AWG-4/0 AWG
Conductor - Copper Flex I Tap Range	2 AWG-4/0 AWG
Conductor - Copper Flex K Run Range	2 AWG-4/0 AWG
Conductor Size	250 KCMIL-250 KCMIL
Conductor - Copper Str Run Range	250 KCMIL-2 AWG
Conductor - Copper Str Run	250 KCMIL-2 AWG
Conductor - Copper Flex M Tap Range	2 AWG-4/0 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Flex I Run Range	2 AWG-4/0 AWG

Conductor - Copper Str Tap Range	250 KCMIL-2 AWG
Conductor - Copper Str Tap	250 KCMIL-2 AWG

Configuration

Connector Type	C-TAP
----------------	-------

Current

Voltage - Maximum	35000
-------------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height inch	2.12 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	24 mm
Dimension - Strip Length inch	1 in
Dimension - Width inch	0.98 in
Dimension - Length Overall inch	0.94 in

General

Trade Name	CRIMPIT™
Die Index	997
Plated	Y
Color Code	Orange
Sub Brand	CRIMPIT
UPC	781810013717
Type	YCHC Series
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810013717
UPC 14 Digit GTIN	00781810013717

Logistics

Minimum Pack Quantity	1
Pallet Quantity	9408
Carton Quantity	24

Product Assets

[Catalog \[English\]](#)

