



YCR2C4W, Copper Jumper Sleeve Reducer, #2 (side A), #4 Sol (side AA)

By Burndy
Catalog # [YCR2C4W](#)

Cu Jumper Loop Sleeve Reducer, #2 - 7 Str Cu(Side A), #4 Sol (Side AA)



Features

- Copper Jumper Sleeve Reducer

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	2 AWG
Conductor - Copper Str Size A Range	2 AWG
Conductor - Copper Solid Size B	4 AWG

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - B Length fraction	1-4/25 in
Dimension - L Length Overall mm	95 mm

Dimension - B Length inch	1.16 in
Dimension - B Outside Diameter inch	0.5 in
Dimension - A Outside Diameter inch	0.38 in
Dimension - Length BB inch	1.1 in
Dimension - Length Overall inch	3.73 in

General

Plated	Y
Trade Name	HYREDUCER™
Die Index	163
Oxide Inhibitor Type	Penetrox A4
UPC	781810014295
Prefilled Oxide Inhibitor	Y
Material	Copper
Plating Type	Tin - Hot Dipped
UPC 14 Digit GTIN	00781810014295

Logistics

Minimum Pack Quantity	1
Pallet Quantity	19200
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)