

YCR32RG5, Aluminum Reducer

By Burndy
Catalog # [YCR32RG5](#)



Aluminum Reducer, Designed for joining (i) Cu to Alum. or ACSR
(ii) Alum or ACSR to Alum. or ACSR, Barrels Partially filled with
PENETROX™ and Sealed

Features

- Aluminum Reducer
- Partially filled with PENETROX Oxide Inhibitor and Sealed

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Str Size A	350 kcmil
Conductor - Copper Str Size A Range	350 kcmil
Conductor - Copper Str Size B	250 kcmil
Conductor - Copper Str Size B Range	250 kcmil
Conductor - ACSR Str Size A	• 336.4 (18/1) Merlin • 336.4 (26/7) Linnet
Conductor Type	• ACSR C Str-Size A • AL C Str-Size A • CU C Str-Size A • ACSR C Str-Size B • AL C Str-Size B • CU C Str-Size B
Conductor - ACSR Str Size A Range	336.4 (18/1) Merlin-336.4 (26/7) Linnet
Conductor - ACSR Str Size B	266.8 (18/1) Waxwing
Conductor - ACSR Str Size B Range	266.8 (18/1) Waxwing
Conductor - AL Str Size A	• 350 kcmil • 397.5 kcmil
Conductor - AL Str Size A Range	350 kcmil-397.5 kcmil
Conductor - AL Str Size B	• 250 kcmil • 266.8 kcmil

Conductor - AL Str Size B Range	• 250 kcmil • 266.8 kcmil
---------------------------------	---

Configuration

Connector Type	Reducer
----------------	---------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - B Length inch	3 in
Dimension - Outside Diameter inch	1.25 in
Dimension - L Length Overall mm	170 mm
Package Height	0.000 in
Dimension - Length BB inch	3 in
Dimension - Length Overall inch	6.69 in

General

Die Index	• 317 • 705
Trade Name	HYREDUCER™
Plated	N
Prefilled Oxide Inhibitor	Y
UPC 12 Digit	781810103968
UPC 14 Digit GTIN	00781810103968
Material	Aluminum
Plating Type	Unplated
UPC	781810103968

Logistics

Minimum Pack Quantity	1
Carton Quantity	10
Pallet Quantity	2940

Product Assets

[Catalog \[English\]](#)