


YCS011R, Aluminum Loop Splice

By Burndy
Catalog # [YCS011R](#)

Al Compression Loop Splice, 80 kcmil ACSR



Features

- Aluminum Compression Loop Splice

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Str Size	80 (8/1) Grouse kcmil
Conductor - ACSR Str Size Range	80 (8/1) Grouse kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - B Length inch	3.55 in
Dimension - Outside Diameter inch	0.7 in

Dimension - L Length Overall mm	182 mm
Dimension - Length Overall inch	7.18 in

General

Die Index	245
Trade Name	HYSPLICE™
Plated	N
Prefilled Oxide Inhibitor	Y
UPC 12 Digit	781810096697
UPC 14 Digit GTIN	00781810096697
Material	Aluminum
Plating Type	Unplated
UPC	781810096697

Logistics

Minimum Pack Quantity	1
Carton Quantity	25
Pallet Quantity	9800

Product Assets

[Catalog \[English\]](#)