

YCS1C, Copper Jumper Sleeve

By Burndy
Catalog # [YCS1C](#)

Cu Jumper Sleeve, #1 AWG Cu Cable, 3.12" L, 164 Index



Features

- Copper Jumper Sleeve

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	1 AWG
Conductor - Copper Str Size	1 AWG

Configuration

Physical Attribute - Number of Crimps Required	4
Connector Type	Splice

Dimensions

Dimension - B Length fraction	1-1/2 in
Dimension - L Length Overall mm	79 mm

Dimension - B Length inch	1.5 in
Dimension - B Outside Diameter inch	0.56 in
Dimension - A Outside Diameter inch	0.56 in
Dimension - Length BB inch	1.5 in
Dimension - Length Overall inch	3.12 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	164
UPC	781810014165
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810014165
UPC 14 Digit GTIN	00781810014165

Logistics

Minimum Pack Quantity	1
Pallet Quantity	14800
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)