



YCS25, Copper Loop Splice

By Burndy
Catalog # [YCS25](#)



CU loop splice connector designed to withstand jumper loop tensile and vibration stresses up to 60 percentage RBS, -3/8 IN L

Features

- Compression Copper Loop Splice
- Designed to withstand jumper loop tensile and vibration stress up to 60 percent of Rated Breaking Strength

Application

For Copper Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	1/0
Conductor Type	• CU C Str-Size • CU C Solid-Size
Conductor - Copper Str Size Range	1/0

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in

Package Width	0.000 in
Dimension - L Length Overall mm	78 mm
Dimension - Outside Diameter inch	0.63 in
Dimension - B Length fraction	1-8/17 in
Dimension - B Length inch	1.47 in
Dimension - Inside Diameter inch	0.41 in
Dimension - Length Overall inch	3.09 in

General

Product Family	Utility Overhead & Underground Distribution>Splices>YCS/YDS (Normal Tension)
Trade Name	HYSPLICE™
Die Index	165
Prefilled Oxide Inhibitor	N
Plated	No
Sub Brand	HYSPLICE
Product Type	Compression
UPC	781810014172
Type	YCS
Construction Material - Main	Copper
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810014172
UPC 14 Digit GTIN	00781810014172

Logistics

Minimum Pack Quantity	1
Pallet Quantity	9800
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)