



YCS25R, Aluminun Sleeve, Staked Cable Stop

By Burndy
Catalog # [YCS25R](#)



HYSPLICE AL sleeve with staked cable stop, designed to withstand jumper loop tensile and vibration stresses. ANSI C119.4 CLASS 2 (PARTIAL TENSION), 7-1/8 IN L.

Features

- HYSPLICE Sleeve designed to withstand jumper loop tensile and vibration stresses
- Made of aluminum with staked-in cable stop
- Pre-Filled with PENETROX Joint Compound and Capped

Application

For ACSR, All Aluminum, 6201, 5005 And Compressed Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	RUS
Certification - ETL	No
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	1/0 (7, 19) AWG
Conductor - AL Str Size Range	1/0 (7, 19) AWG
Conductor - ACSR Str Size	1/0 (6/1) Raven AWG
Conductor - ACSR Str Size Range	1/0 (6/1) Raven AWG

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	180 mm
Dimension - Outside Diameter inch	0.62 in
Dimension - B Length inch	3.48 in
Dimension - Length Overall inch	7.09 in

General

Trade Name	HYSPLICE™
Die Index	243
Prefilled Oxide Inhibitor	Y
Plated	N
Sub Brand	HYSPLICE
UPC	781810820513
Type	YCS-R
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810820513
UPC 14 Digit GTIN	00781810820513

Logistics

Minimum Pack Quantity	1
Pallet Quantity	9800
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)