

YCS25RLELN, Aluminum Sleeve, Staked Cable Stop

By Burndy
Catalog # [YCS25RLELN](#)

HYSPLICE Aluminum sleeve with staked cable stop, designed to withstand jumper loop tensile and vibration stresses. ANSI C119.4 CLASS 2 (PARTIAL TENSION).

Features

- Aluminum Sleeve
- Staked Cable Stop

Specifications


Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Cmpt Size	1/0 AWG
Conductor - ACSR Cmpt Size Range	1/0 AWG
Conductor - ACSR Str Size	1/0 (6/1) Raven AWG
Conductor - ACSR Str Size Range	1/0 (6/1) Raven AWG
Conductor - AL Str Size	1/0 AWG
Conductor - AL Str Size Range	1/0 AWG

Configuration

Connector Type	Splice
----------------	--------



Dimensions

Dimension - L Length Overall	158 mm
Dimension - Length Overall	6.22 in

General

Die Index	247
Trade Name	UNISPLICE™
Plated	N
Prefilled Oxide Inhibitor	Y
UPC 12 Digit	781810250167
UPC 14 Digit GTIN	00781810250167
Material	Aluminum
Plating Type	Unplated
UPC	781810250167

Logistics

Minimum Pack Quantity	1
Carton Quantity	25
Pallet Quantity	9800

Product Assets

[Catalog \[English\]](#)