


YCS271R, Copper Loop Splice

By Burndy
Catalog # [YCS271R](#)

Al Compression Loop Splice, 159 kcmil ACSR



Features

- Copper Loop Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Str Size	159 (12/7) Guinea kcmil
Conductor - ACSR Str Size Range	159 (12/7) Guinea kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Dimension - L Length Overall	224 mm
Dimension - B Length inch	4.31 in
Dimension - Outside Diameter inch	1.25 in
Dimension - Length Overall inch	8.80 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	317
UPC	781810178850
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810178850
UPC 14 Digit GTIN	00781810178850

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2400
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)