




YCS27R, Aluminum Sleeve, Staked Cable Stop

By Burndy
Catalog # [YCS27R](#)

Al Jumper sleeve, 3/0 6-1 str, 5-11/16"L, 247 index



Features

- Aluminum Sleeve
- Staked Cable Stop

Application

HYSPLICE sleeve designed to withstand jumper loop tensile and vibration stresses

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Certification - UL Recognized	No
Industry Standard(s)	RUS
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Str Size	3/0 (6/1) Pigeon AWG 4/0 (6/1) Penguin AWG 80 (8/1) Grouse kcmil 101.8 (12/7) Petrel kcmil 110.8 (12/7) Minorca kcmil
Conductor - ACSR Str Size Range	3/0 (6/1) Pigeon AWG-110.8 (12/7) Minorca kcmil
Conductor - AL Str Size	3/0 AWG
Conductor - AL Str Size Range	3/0 AWG

Configuration

Connector Type Splice

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.78 in
Dimension - L Length Overall mm	146 mm
Package Height	0.000 in
Dimension - B Length inch	2.81 in
Dimension - Length Overall inch	5.75 in

General

Die Index	247
Trade Name	HYSPLICE™
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Plated	N
Construction Material - Main Type	Aluminum YCS-R
UPC 12 Digit	781810015025
UPC 14 Digit GTIN	00781810015025
Material	Aluminum
Plating Type	Unplated
UPC	781810015025

Logistics

Minimum Pack Quantity	25
Carton Quantity	25
Pallet Quantity	7400

Product Assets

[Catalog \[English\]](#)