

YCS28, Copper Loop Splice

By Burndy
Catalog # [YCS28](#)



CU loop splice connector designed to withstand jumper loop tensile and vibration stresses up to 60 percentage RBS, 3-1/8 IN L

Features

- Copper Loop Splice
- Designed to withstand jumper loop tensile and vibration stress up to 60 percent of Rated Breaking Strength

Application

For Copper Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG

Configuration

Physical Attribute - Number of	3
Crimps Required	
Connector Type	Splice

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in

Package Width	0.000 in
Dimension - L Length Overall mm	78 mm
Dimension - A Outside Diameter	0.89 in
inch	
Dimension - B Length fraction	1-8/17 in
Dimension - B Length inch	1.47 in
Dimension - B Outside Diameter	0.89 in
inch	
Dimension - Length Overall inch	3.09 in

General

Product Family	Utility Overhead & Underground Distribution>Splices>YCS/YDS (Normal Tension)
Trade Name	HYSPLICE™
Die Index	168
Prefilled Oxide Inhibitor	N
Plated	No
Sub Brand	HYSPLICE
Product Type	Compression
UPC	781810014219
Type	YCS
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810014219
UPC 14 Digit GTIN	00781810014219

Logistics

Minimum Pack Quantity	1
Pallet Quantity	5800
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)