



YCS28A, Aluminum Sleeve

By Burndy
Catalog # [YCS28A](#)



Aluminum sleeve designed to withstand jumper loop tensile and vibration stresses. Made of aluminum with staked cable stop. ANSI C119.4 CLASS 1A(PARTIAL TENSION),Die Index: 249.

Features

- HYSPLICE Sleeve designed to withstand jumper loop tensile and vibration stresses
- Made of aluminum with staked-in cable stop
- Pre-Filled with PENETROX Joint Compound and Capped

Application

For All Aluminum, Compressed And Compact Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	4/O AWG
-------------------------	---------

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
----------------	----------

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	102 mm
Dimension - Outside Diameter	0.6 in
Dimension - B Length inch	1.94 in
Dimension - Length Overall	4 in

General

Trade Name	HYSPLICE™
Die Index	249
Prefilled Oxide Inhibitor	Y
Plated	N
Sub Brand	HYSPLICE
UPC	781810820537
Type	YCS-A
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810820537
UPC 14 Digit GTIN	00781810820537

Logistics

Minimum Pack Quantity	25
Pallet Quantity	11600
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)