YCS28R, Aluminum Sleeve, Staked Cable Stop



By Burndy
Catalog # YCS28R

HYSPLICE AL sleeve with staked cable stop, designed to withstand jumper loop tensile and vibration stresses. ANSI C119.4 CLASS 2 (PARTIAL TENSION), Index: 249.

Features

- HYSPLICE Sleeve designed to withstand jumper loop tensile and vibration stresses
- Made of aluminum with staked-in cable stop
- Pre-Filled with PENETROX Joint Compound and Capped

Application

For ACSR, All Aluminum, 6201, 5005 And Compressed Conductors

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Industry Standard(s)	RUS
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Str Size	4/0 (6/1) Penquin AWG
Conductor - AL Str Size	4/0 AWG

Configuration

Connector Type	Splice

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.87 in
Dimension - L Length Overall mm	146 mm
Package Height	0.000 in
Dimension - B Length inch	2.81 in
Dimension - Length Overall inch	5.75 in

General

Die Index	249
Trade Name	HYSPLICE™
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Plated	N
Type	YCS-R
UPC 12 Digit	781810820544
UPC 14 Digit GTIN	00781810820544
Material	Aluminum
Plating Type	Unplated
UPC	781810820544

Logistics

Minimum Pack Quantity	1
Carton Quantity	25
Pallet Quantity	7400

Product Assets

Catalog [English]

© 2026 Hubbell Incorporated. All rights reserved