

YCS29, Copper Loop Splice

By Burndy
Catalog # [YCS29](#)



CU loop splice connector designed to withstand jumper loop tensile and vibration stresses up to 60 percentage RBS, 3-5/8 IN L

Features

- Copper Loop Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	250 kcmil
Conductor - Copper Str Size	250 kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	1-44/83 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	92 mm

Dimension - B Length inch	1.53 in
Dimension - B Outside Diameter inch	0.95 in
Dimension - A Outside Diameter inch	0.95 in
Dimension - Length BB inch	1.53 in
Dimension - Length Overall inch	3.62 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	169
UPC	781810014226
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810014226
UPC 14 Digit GTIN	00781810014226

Logistics

Minimum Pack Quantity	1
Pallet Quantity	4350
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)