


YCS2R, Aluminum Sleeve, Staked Cable Stop

By Burndy
Catalog # [YCS2R](#)

Al Jumper sleeve, #2, 6-1, 7-1 STR, 4-1/2"L, 239 index



Features

- Aluminum Sleeve
- Staked Cable Stop

Application

The sleeves designed to withstand jumper loop tensile and vibration stresses.

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Certification - UL Recognized	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - AAAC 5005 Size Range	77.47 (7) kcmil
Conductor - AAAC 6201 Size	77.47 (7) kcmil
Conductor - ACSR Str Size	• 2 (6/1) Sparrow AWG • 2 (7/1) Sparate AWG
Conductor - AL Str Size	2 AWG
Conductor - AAAC 5005 Size	77.47 (7) kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter	0.5 in
Dimension - L Length Overall	125 mm
Package Height	0.000 in
Dimension - B Length inch	2.38 in
Dimension - Length Overall	4.91 in

General

Die Index	239
Trade Name	HYSPLICE™
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Plated	N
Construction Material - Main	Aluminum
Type	YCS-R
UPC 12 Digit	781810014974
UPC 14 Digit GTIN	00781810014974
Material	Aluminum
Plating Type	Unplated
UPC	781810014974

Logistics

Minimum Pack Quantity	1
Carton Quantity	25
Pallet Quantity	24000

Product Assets

[Catalog \[English\]](#)