



YCS30, Copper Loop Splice

By Burndy
Catalog # [YCS30](#)



CU loop splice connector designed to withstand jumper loop tensile and vibration stresses up to 60 percentage RBS, 5-3/8 IN L

Features

- Copper Loop Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	300 kcmil
Conductor - Copper Str Size	300 kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	1-11/25 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	92 mm

Dimension - B Length inch	1.44 in
Dimension - B Outside Diameter inch	1.05 in
Dimension - A Outside Diameter inch	1.05 in
Dimension - Length BB inch	1.44 in
Dimension - Length Overall inch	3.62 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	170
UPC	781810014233
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810014233
UPC 14 Digit GTIN	00781810014233

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2900
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)