



YCS31, Copper Loop Splice

By Burndy
Catalog # [YCS31](#)

CU loop splice connector designed to withstand jumper loop tensile and vibration stresses up to 60 percentage RBS, Index: 267

Features

- Copper Loop Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	350 kcmil
Conductor - Copper Str Size	350 kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	2-16/39 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	138 mm

Dimension - B Length inch	2.41 in
Dimension - B Outside Diameter inch	1.17 in
Dimension - A Outside Diameter inch	1.17 in
Dimension - Length BB inch	2.41 in
Dimension - Length Overall inch	5.44 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	267
UPC	781810014240
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810014240
UPC 14 Digit GTIN	00781810014240

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1740
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)