

YCS32, Copper Loop Splice

By Burndy
Catalog # [YCS32](#)



CU loop splice connector designed to withstand jumper loop tensile and vibration stresses up to 60 percentage RBS, Index: 209

Features

- Copper Loop Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	400 kcmil
Conductor - Copper Str Size	400 kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	2-64/81 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Dimension - L Length Overall mm	145 mm
Dimension - B Length inch	2.79 in
Dimension - B Outside Diameter inch	1.24 in
Dimension - A Outside Diameter inch	1.24 in
Dimension - Length Overall inch	5.72 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	209
UPC	781810014264
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810014264
UPC 14 Digit GTIN	00781810014264

Logistics

Minimum Pack Quantity	10
Pallet Quantity	1160
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)