



YCS321R, Aluminum Sleeve, Staked Cable Stop

By Burndy
Catalog # [YCS321R](#)

HYSPLICE AL sleeve with staked cable stop, designed to withstand jumper loop tensile and vibration stresses. ANSI C119.4 CLASS 2 (PARTIAL TENSION), 6-1/2 IN L.

Features

- HYSPLICE Sleeve designed to withstand jumper loop tensile and vibration stresses
- Made of aluminum with staked-in cable stop
- Pre-Filled with PENETROX Joint Compound and Capped

Application

For ACSR, All Aluminum, 6201, 5005 And Compressed Conductors

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor


Conductor - ACSR Str Size	336.4 (18/1) Merlin kcmil
Conductor - AL Str Size	336.4 kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Length	0.000 in
----------------	----------



Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter	1.12 in
Dimension - L Length Overall	164 mm
Package Height	0.000 in
Dimension - B Length fraction	3-18/25 in
Dimension - B Length inch	3.18 in
Dimension - Length Overall	6.47 in
inch	

General

Die Index	490
Trade Name	HYSPLICE™
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Plated	N
Type	YCS-R
UPC 12 Digit	781810820551
UPC 14 Digit GTIN	00781810820551
Material	Aluminum
Plating Type	Unplated
UPC	781810820551

Logistics

Minimum Pack Quantity	25
Carton Quantity	25
Pallet Quantity	3600

Product Assets

[Catalog \[English\]](#)